

Test	Ambient Temperature and Relative Humidity	Target Temperature	Test Load Packages ¹ Included
Quality Inspection	Not applicable	Not applicable	Not applicable
<i>Energy Performance Testing under normal operating conditions</i>			
Pre-test conditioning	+10°C / RH ≤75%	Not applicable	No
Steady-state operation test – Low ambient / Normal voltage condition	+10°C / RH ≤75%	Stabilization at an average temperature of +4°C (between +0°C and +6°C)	No
Steady-state operation test – Medium ambient / Normal voltage condition	+16°C / RH ≤75%	Stabilization at an average temperature of +4°C (between +0°C and +6°C)	No
Steady-state operation test – High ambient / Normal voltage condition	+32°C / RH ≤75%	Stabilization at an average temperature of +4°C (between +0°C and +6°C)	No
<i>Refrigerating/Freezing Performance Testing</i>			
Autonomy test	+32°C / RH ≤75%	Test discontinue when > +12°C	No
Pull-down test	+32°C / RH ≤75%	Stabilization < +4°C	No
Freezing capacity test (for Refrigerator-freezers only)	+32°C / RH ≤75%	Stabilization < -15°C	Yes
Over-voltage test	+32°C / RH ≤75%	Not applicable	No
Under-voltage test	+32°C / RH ≤75%	Not applicable	No
Steady-state operation test – Harsh ambient / Normal voltage condition	+43°C / RH=85%	Stabilization at an average temperature ≤ 4°C (between +0°C and +6°C)	No

¹ Test load packages are prepared in accordance with IEC 62552-1 Annex C