



SPRINT CELL

to give the perfect blend needed to get the best result, whilst eliminating surface bruising. It can also reduce overall cutting pressure, whilst the Sprintface skin prevents the ink being absorbed. The sheets are colour coded to identify the different shore hardness.


Benefits of using high quality ejection products Sprintcell and Vulkollan

- Long runs no problem can out last the die life
- Ideal for multiple fit backs
- Also supplied with self-adhesive
- Not susceptible to colour change from UV exposure (Sprintcell)
- Reduction in transport and waste nicks required for sheet transport
- Greater balance of waste through the stripping unit
- Reduces board swarf, angel hair, protects surface from cracking and bruising
- Reduced waste over all

Sprintcell (Rotary application) has Sprintface technology. It is very wear resistant when using it for long runs. When using the Sprintcell in waste stripping areas, you can reduce the trim needed and aids waste ejection. The Sprintcell skin prevents ink being absorbed onto the surface. The sheets are colour coded to identify the different shore hardness.

Sprintcell (Folding Carton and Flat Bed corrugated) has Sprintface technology – This gives overall control whilst ejecting any substrate from the die. Our vast range of shore hardness allows you

VULKOLLAN RUBBER



Available in RG35, RG45, RG55 & RG65 with or without adhesive backing. Sheet Size 250mm X 500mm

Our Vulkollan is very high quality rubber. It is used to eject sheets from the die in slots on flat bed and rotary tooling. When the Vulkollan is under pressure it will not expand outwards, preventing cutting rule joints spreading. The Vulkollan can be water jetted or cut using an oscillating knife.

| | | | |
|--|--|--|--|
| SprintCell 500 x 500 x 7.0mm 15 sh white | SprintCell 500 x 500 x 3.0mm 25 sh red | SprintCell 500 x 500 x 4.0mm 35 sh green | SprintCell 500 x 500 x 22.0mm 40 sh orange |
| SprintCell 500 x 500 x 10.0mm 15 sh white | SprintCell 500 x 500 x 6.0mm 25 sh red | SprintCell 500 x 500 x 5.0mm 35 sh green | SprintCell 500 x 500 x 27.0mm 40 sh orange |
| SprintCell 500 x 500 x 11.0mm 15 sh white | SprintCell 500 x 500 x 7.0mm 25 sh red | SprintCell 500 x 500 x 7.0mm 35 sh green | SprintCell 500 x 500 x 35.0mm 40 sh orange |
| SprintCell 500 x 500 x 12.0mm 15 sh white | SprintCell 500 x 500 x 8.0mm 25 sh red | SprintCell 500 x 500 x 8.0mm 35 sh green | SprintCell 500 x 500 x 35.0mm 40 sh orange |
| SprintCell 500 x 500 x 13.0mm 15 sh white | SprintCell 500 x 500 x 10.0mm 25 sh red | SprintCell 500 x 500 x 10.0mm 35 sh green | SprintCell 500 x 500 x 10.0mm 45 sh brown |
| SprintCell 500 x 500 x 14.0mm 15 sh white | SprintCell 500 x 500 x 12.0mm 25 sh red | SprintCell 500 x 500 x 12.0mm 35 sh green | SprintCell 500 x 500 x 11.0mm 45 sh brown |
| SprintCell 500 x 500 x 16.0mm 15 sh white | SprintCell 500 x 500 x 14.0mm 25 sh red | SprintCell 500 x 500 x 13.0mm 35 sh green | SprintCell 500 x 500 x 16.0mm 45 sh brown |
| SprintCell 500 x 500 x 22.0mm 15 sh white | SprintCell 500 x 500 x 15.0mm 25 sh red | SprintCell 500 x 500 x 15.0mm 35 sh green | SprintCell 500 x 500 x 17.0mm 45 sh brown |
| SprintCell 500 x 500 x 27.0mm 15 sh white | SprintCell 500 x 500 x 16.0mm 25 sh red | SprintCell 500 x 500 x 16.0mm 35 sh green | SprintCell 500 x 500 x 22.0mm 45 sh brown |
| SprintCell 500 x 500 x 35.0mm 15 sh white | SprintCell 500 x 500 x 17.0mm 25 sh red | SprintCell 500 x 500 x 17.0mm 35 sh green | SprintCell 500 x 500 x 27.0mm 45 sh brown |
| SprintCell 500 x 500 x 7.0mm 20 sh yellow | SprintCell 500 x 500 x 18.0mm 25 sh red | SprintCell 500 x 500 x 18.0mm 35 sh green | SprintCell 500 x 500 x 35.0mm 45 sh brown |
| SprintCell 500 x 500 x 8.0mm 20 sh yellow | SprintCell 500 x 500 x 22.0mm 25 sh red | SprintCell 500 x 500 x 22.0mm 35 sh green | SprintCell 500 x 500 x 10.0mm 50 sh grey |
| SprintCell 500 x 500 x 10.0mm 20 sh yellow | SprintCell 500 x 500 x 27.0mm 25 sh red | SprintCell 500 x 500 x 27.0mm 35 sh green | SprintCell 500 x 500 x 16.0mm 50 sh grey |
| SprintCell 500 x 500 x 11.0mm 20 sh yellow | SprintCell 500 x 500 x 35.0mm 25 sh red | SprintCell 500 x 500 x 35.0mm 35 sh green | SprintCell 500 x 500 x 17.0mm 50 sh grey |
| SprintCell 500 x 500 x 12.0mm 20 sh yellow | SprintCell 500 x 500 x 7.0mm 30 sh blue | SprintCell 500 x 500 x 7.0mm 40 sh orange | SprintCell 500 x 500 x 27.0mm 50 sh grey |
| SprintCell 500 x 500 x 14.0mm 20 sh yellow | SprintCell 500 x 500 x 10.0mm 30 sh blue | SprintCell 500 x 500 x 10.0mm 40 sh orange | SprintCell 500 x 500 x 22.0mm 50 sh grey |
| SprintCell 500 x 500 x 15.0mm 20 sh yellow | SprintCell 500 x 500 x 11.0mm 30 sh blue | SprintCell 500 x 500 x 11.0mm 40 sh orange | SprintCell 500 x 500 x 35.0mm 50 sh grey |
| SprintCell 500 x 500 x 16.0mm 20 sh yellow | SprintCell 500 x 500 x 14.0mm 30 sh blue | SprintCell 500 x 500 x 14.0mm 40 sh orange | SprintCell 500 x 500 x 35.0mm 50 sh grey |
| SprintCell 500 x 500 x 17.0mm 20 sh yellow | SprintCell 500 x 500 x 16.0mm 30 sh blue | SprintCell 500 x 500 x 15.0mm 40 sh orange | |
| SprintCell 500 x 500 x 22.0mm 20 sh yellow | SprintCell 500 x 500 x 20.0mm 30 sh blue | SprintCell 500 x 500 x 16.0mm 40 sh orange | |
| SprintCell 500 x 500 x 27.0mm 20 sh yellow | SprintCell 500 x 500 x 22.0mm 30 sh blue | SprintCell 500 x 500 x 18.0mm 40 sh orange | |
| SprintCell 500 x 500 x 35.0mm 20 sh yellow | SprintCell 500 x 500 x 27.0mm 30 sh blue | SprintCell 500 x 500 x 18.0mm 40 sh orange | |
| | SprintCell 500 x 500 x 35.0mm 30 sh blue | SprintCell 500 x 500 x 20.0mm 40 sh orange | |

Contact our UK customer service team

01933 273444

Becky: becky.webb@candtmatrix.co.uk

Emma: emmaclose@candtmatrix.co.uk

C&T

MATRIX

SHEET RUBBER